


## TXP-2 Tap Out Actuator



The implementation of Precimeter Technology provides many advantages

- Quality improvements
- Increased productivity
- Documentation of the process
- Raw material savings
- Energy savings
- Better use of manpower

# TXP-2 Tap Out Actuator



Head box tap out control with TXP-2 and ProH sensor

This small and compact Tap Out Actuator is primarily used for control of metal flow through a pin plug valve in head box applications.



## Technical Specifications

Stroke:	50 mm (2")
Positioning:	Stepper motor
Closing force:	Up to 35 N (8 lbs)
Ambient temperature:	175 °C (350 °F)
Power requirement:	18-32 VDC / 1.2 mA
Analog input:	4-20 mA
Analog output:	4-20 mA feed back position signal
Digital inputs:	Analog enable / move pin according to 4-20mA. Calibrate to closed or open position
Digital output:	Temperature alarm 65 °C (150 °F)

**TXP-2 includes** one heavy duty connector and mating control box.

## Contact Precimeter Group

### EASTERN AND CENTRAL EUROPE DIE CASTING AND EM PUMPS

Carli Precimeter GmbH  
Kirberg 5/ D-51674 Wiehl/ DE  
Phone: +49-2262-701624 Fax: +49-2262-701625

### WESTERN EUROPE, MIDDLE EAST, AFRICA, ASIA AND AUSTRALIA

Precimeter Control AB  
Östra Hamnen 7/ SE-475 42 Hönö/ SE  
Phone: +46-31-764 55 20 Fax: +46-31-764 55 29  
[www.precimeter.com](http://www.precimeter.com)  
[info@precimeter.com](mailto:info@precimeter.com)

### NORTH, CENTRAL AND SOUTH AMERICA

Sentech Precimeter Inc.  
2215 S. 48th Str. #C / Tempe, AZ 85282/ U.S.A  
Phone: +1 (480) 829-1923 Fax: +1 (480) 894-5546

## Local Precimeter Contact